

# SSGT Range and Selection

Our SSGT stainless steel filtered grease traps come in a range of sizes to suit all applications and work areas. When using the chart to determine the best model for you, choose the largest that will fit whilst leaving 100mm all round to allow for unclipping the lid. Please allow height **K** for removal of the filter cassette.




Diagram Measurement

|        | A    | B   | C   | D    | E   | F       | G      | H  | J  | K   |
|--------|------|-----|-----|------|-----|---------|--------|----|----|-----|
| SSGT1  | 150  | 150 | 150 | 225  | 150 | 120     | 40     | 35 | 35 | 150 |
| SSGT2  | 350  | 330 | 200 | 375  | 350 | 163-330 | 50     | 45 | 65 | 200 |
| SSGT4  | 500  | 400 | 200 | 525  | 450 | 163-330 | 50     | 45 | 65 | 200 |
| SSGT6  | 500  | 400 | 300 | 525  | 450 | 233-400 | 50/110 | 45 | 65 | 300 |
| SSGT8  | 500  | 400 | 400 | 525  | 450 | 333-500 | 50/110 | 45 | 65 | 400 |
| SSGT12 | 750  | 400 | 400 | 775  | 450 | 333     | 110    | 70 | 70 | 400 |
| SSGT16 | 1000 | 400 | 400 | 1025 | 450 | 333     | 110    | 70 | 70 | 400 |
| SSGT20 | 1200 | 400 | 400 | 1225 | 450 | 333     | 110    | 70 | 70 | 400 |

Application

|        | Domestic Kitchen / Coffee Machine | Takeaway | Dishwasher | Small Kitchen 10-50 Covers | Medium Kitchen 51-100 Covers | Large Kitchen 101-150 Covers | Extra Large Kitchen 151+ Covers |
|--------|-----------------------------------|----------|------------|----------------------------|------------------------------|------------------------------|---------------------------------|
| SSGT1  | ✓                                 |          |            |                            |                              |                              |                                 |
| SSGT2  | ✓                                 | ✓        |            | ✓                          |                              |                              |                                 |
| SSGT4  |                                   | ✓        |            | ✓                          |                              |                              |                                 |
| SSGT6  |                                   | ✓        |            | ✓                          | ✓                            |                              |                                 |
| SSGT8  |                                   | ✓        | ✓          | ✓                          | ✓                            |                              |                                 |
| SSGT12 |                                   |          | ✓          | ✓                          | ✓                            | ✓                            | ✓                               |
| SSGT16 |                                   |          | ✓          | ✓                          | ✓                            | ✓                            | ✓                               |
| SSGT20 |                                   |          | ✓          | ✓                          | ✓                            | ✓                            | ✓                               |

## Installation

SSGT stainless steel filtered grease traps come fully assembled and ready to fit by a qualified plumber. If fitting into an existing system, check first that drain pipes on the outlet side have been cleaned. Set stainless steel brackets (*supplied*) to the required inlet/outlet height. Connect to inlet and outlet using standard Multifit connectors (*not supplied*). The low level 15mm pipe must be connected to the main drain with a shut off valve (*not supplied*). This will aid the deep cleaning operation. Once fitted, return the warranty card supplied with the unit to activate customer support and 10 year manufacturers warranty.

Stainless steel filtered grease traps are designed to be compatible with the drain dosing systems for the timed injection of multi strain biological grease digesting liquid into the grease traps. Please ask for details and installation instructions. (Adjustable mounting feet not available on the SSGT1, SSGT12, SSGT16, SSGT20 Models)